



## Inner rings IR60X68X45-XL (Series IR)

precision machined, to DIN 620

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

|                  |       |   |
|------------------|-------|---|
| d                | 60 mm |   |
| F                | 68 mm | Tolerance of raceway F in $\mu\text{m}$ : -10/-21 |
| B                | 45 mm |   |
| <br>             |       |   |
| r <sub>min</sub> | 1 mm  |   |
| <br>             |       |   |
| m                | 276 g | Mass  |

