3418 : Magnetic screwdrivers














The + product :

Magnetic tip securing the screw, for comfortable and fast screwing.

Graded shank, handy for quick measuring.

Shank in silicon carbon steel for greater torsional strength.

Description

Ergonomic hexagon-shaped grip: broader in its central part for enhanced palm grip and **force application**, and narrower close to the shank for **quick rotation** between thumb and index.

Bimaterial grip, for more **comfortable** handling, and **non-slip** with high resistance to cold, impact, abrasion, solvents, and hydrocarbons.

Effective rotation in the palm with its **sliding thrust zone**.

Integral grip moulded directly onto the shank with dual opposite flats.

Hexagon nut for easier unlocking of jammed screws using a wrench (not supplied).

Burnished tip to reinforce its strength and prevent chromium from peeling, **ribbed** for better locking in the screw head.

Complies with the ISO 8764, ISO 2380 and EN 60900 standards (ref. 341806 1000V insulated screwdriver) guaranteeing **high quality** tools and **secured** use.

Supplied in reusable **textile pouch** (set of 8 screwdrivers, ref. 341820).

References

Sku	Description	kg
341820	Set of 8 magnetic screwdrivers (341801 to 341808) in textile pouch	0,900
341801	Magnetic screwdriver PZ2 x 38 - 106 mm	0,063
341802	Magnetic screwdriver 5.5 X 38 - 106 mm	0,058
341803	Magnetic screwdriver PZ1 X 100 - 209 mm	0,083

Sku	Description	kg
341804	Magnetic screwdriver 5.5 X 100 - 209 mm	0,078
341805	Magnetic screwdriver 6.5 X 150 - 259 mm	0,108
341806	1000V insulated screwdriver 3 X 80 - 170 mm	0,043
341807	Magnetic screwdriver PZ2 X 100 - 209 mm	0,096
341808	Magnetic screwdriver 8 X 150 - 269 mm	0,155
382652	Fabric pouch for small tools	0,200

