



MASTER LEDspot MV

MAS LEDspotMV VLE D 3.5-35W GU10 840 40D

Delivering a warm, halogen-like accent beam, MASTER LEDspot MV is a perfect fit for spot lighting (track, corridors, lift lobbies, display cases and cabinets) in the hospitality industry. It is particularly suitable to public areas where the light is on 24/7, such as lobbies, corridors, stairwells. MASTER LEDspot MV delivers huge energy savings and minimizes maintenance cost without any compromise on brightness, enabling hospitality owners to achieve a return on their investment within one year. These LEDspots are compatible with most existing fixtures with a GU10 holder and designed as a retrofit replacement for halogen or incandescent spots. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Product data

• General Information

Cap-Base	GU10
Bulb Shape	PAR16 [PAR 2 inch]
Nominal Lifetime (Nom)	35000 h
Switching Cycle B50L70	50000X
Technical Type	3.5-35W

• Light Technical

Color Code	840 [CCT of 4000K (841)]
Beam Angle (Nom)	40 °
Luminous Flux (Nom)	330 lm
Luminous Flux (Rated) (Nom)	330 lm
Luminous Intensity (Nom)	550 cd
Color Designation	Cool White (CW)
Rated Beam Angle	40 °
Correlated Color Temperature (Nom)	4000 K
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux In 90° Cone (Rated)	290 lm

• Operating and Electrical

Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	3.5 W
Lamp Current (Nom)	19 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm Up Time To 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.8
Voltage (Nom)	220-240 V

• Controls and Dimming

Dimmable	Yes
----------	-----

• Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Energy Efficiency Label (EEL)	A++
Energy Consumption kWh/1000 h	4 kWh

• Product Data

Full product code	871869656306900
Order product name	MAS LEDspotMV VLE D 3.5-35W GU10 840 40D
EAN/UPC - Product	8718696563069

PHILIPS

MASTER LEDspot MV

Order code 929001215702
Numerator - Quantity Per Pack 1
Numerator - Packs per outer box 10


Material Nr. (12NC) 929001215702
Net Weight (Piece) 0.036 kg

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient

- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Dimensional drawing




GU10 230V 4W-35W 260lm 40D 4000K GU10 D


Product	D	Ø
MAS LEDspotMV VLE D 3.5-35W GU10 840 40D	50 mm	56 mm

Accent Lighting - Spots

1 x GU10 3.5W 2700K 40D

1 x 315 lm





© 2016 Philips Lighting Holding B.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2016, September 16
data subject to change