





LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
CM		53										B	REV PER EC 0L30-0067-96	10-4-96		JH	RS



TYPICAL RECEPTACLE CAVITY SECTION
(DIMENSIONS REFERENCE ONLY)


MATING CONNECTOR INTERFACE



3-DIMENSIONAL MODELS
NTS

.199	5.05	-	-
.145	3.68	.810	20.57
.062	1.57	.345	8.76
.010	0.25	.340	8.64
.005	0.13	.200	5.08
IN	MM	IN	MM

CONVERSION TABLE



770419-1		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON : 2 PLC DEC ± .005 3 PLC DEC ± .005 ANGLES ± .005		AMP INCORPORATED Harrisburg, Pa. 17105	
NYLON, UL 94V-2		NAME RECEPTACLE, 2 CIRCUIT, .062 PIN AND SOCKET	
NATURAL		DRAWING NO 770419	
SCALE 5:1		SHEET 1 OF 1	