

Hose holder with cover - WP-BASE C PA HF 13,0 BK - 3240959

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Hose holder with cover

Image shows WP-TCC PA HF 10.0 BK version



Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 710664
Weight per Piece (excluding packing)	4.13 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Hole diameter	5.5 mm
Diameter	13 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

General

Color	black
Components	Halogen-free
Inflammability class according to UL 94	V0
Material	PA

Hose holder with cover - WP-BASE C PA HF 13,0 BK - 3240959

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC000127
ETIM 5.0	EC000127

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals


Approvals

UL Recognized

Ex Approvals

Approvals submitted

Approval details



Accessories

Accessories

Corrugated pipe

Hose holder with cover - WP-BASE C PA HF 13,0 BK - 3240959

Accessories

Protective hose - WP-PA HF 13,0 BK - 3240681



Polyamide protective hose, inflammability class V0, UV resistant, 1 Pcs. / Pkt. = roll à 50 m

Protective hose - WP-PA HF-HB 13,0 BK - 3240839



Polyamide protective hose, inflammability class HB, UV resistant, 1 Pcs. / Pkt. = roll à 50 m
