



DATASHEET:-

SIP FX EH Mobile Welding Fume Extractor

Manufacturers Part Number 05802

Product Details:

Mobile professional purification system for welding fume extraction.

Fitted with 3 metre multi-directional 160mm dia arm with hood & air flow dampener.

Heavy Duty powder coated steel construction including wheel, handles & digital control panel.

High Performance Centrifugal Extraction Fan Encased in a Soundproof Compartment.

3 Stage Filtering; Aluminium Spark Arrestor, Corrugated Polyester Fibre Pre-Filter & HEPA Absolute Filter 99.5% Efficient.

Perfect for professional Welding Fume Extraction.

Specification:

Supply: 230v 13A.

Power: 1.1 kW.

Max Flow Rate: 2500 m³/h.

Max Suction: 1200 m³/h.

Filtration: 99.5%.

Noise: 73dB.

Boxed Dimensions: 856 x 835 x 505mm.

Weight: 85kg.

1 Year Warranty.