

Han-Eco 10B-HTE-for SL-M40



Image is for illustration purposes only. Please refer to product description.

Part number	19 43 010 0448
Specification	Han-Eco 10B-HTE-for SL-M40
HARTING eCatalogue	https://harting.com/19430100448

Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Eco® B
Type of hood/housing	Hood

Version

Size	10 B
Version	Top entry
Number of cable entries	1
Cable entry	1x M40
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0



Pushing Performance
Since 1945

Specifications and approvals

Specifications	IEC 61984
	EN 45545-2 Fire protection on railway vehicles
Approvals	CE

Commercial data

Packaging size	1
Net weight	117 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140178090
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466