

Features

- 2 Gang
- Switched
- Double Pole
- Twin Earth
- Antique Brass Plate Finish
- Black Insert
- Decorative Victorian plate

RS PRO Plug Sockets

RS Stock No.: 0845497



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Fits standard 25mm 2 gang back boxes
- Suitable for use with standard UK 13A plug tops

General Specifications

Dimensions (mm)	149 (W) x 91 (H) x 27 (D)
Plate Dimensions (mm)	146 (W) x 88 (H) x 8 (D)
Dimensions With Gasket (mm)	149 (W) x 91 (H) x 9 (D)
Plate Fixing Centres (mm)	120.6
Style	Victorian
Finish	Antique Brass
Insert Colour	Black
Gasket Colour	Black
Anti Microbial Certified	No
Warranty (Years)	20

Mechanical Specifications

Termination Type	Screw
Terminal Size (mm)	Ø5
Terminal Torque Value (Nm)	2
Terminal Capacity - Solid (mm²)	3 x 2.5 or 2 x 4
Twin Earth Terminals	Yes
Double Pole Switch	Yes
Minimum Back Box Depth (mm)	25
Ingress Protection	IP20
Operational Temperature (°C)	-5 to +40

Electrical Specifications

Frequency (Hz)	50
Resistive Load Rating (A)	13

Approvals

Standards Met	BS 1363-2
---------------	-----------