

55007

# Padholder, 235 mm, , Orange



An excellent tool for cleaning walls and tanks. Often used to scrub stubborn dirt e.g. pastry, meat, sticky glucose type ingredients. The swivel neck allows the operator to clean underneath equipment. It is designed to hold a scouring pad of varying roughness. The clip mechanism is stainless steel and is very robust. This mechanism prevents the pad from falling off once heavy with water.

# Technical Data

<b>Item Number</b>	55007
<b>Material</b>	Polypropylene Stainless Steel Nylon
<b>Suitable for Food Contact (EU 1935/2004), DoC <sup>1</sup></b>	No
<b>Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice</b>	Yes
<b>FDA compliant raw material (CFR 21)</b>	Yes
<b>Use of Phthalates (e.g. Bisphenol A)</b>	No
<b>Is Halal compliant</b>	Yes
<b>Box Quantity</b>	10 Pcs.
<b>Quantity per Pallet (80 x 120 x 200 cm)</b>	1040 Pcs
<b>Quantity Per Layer (Pallet)</b>	80 Pcs.
<b>Box Length</b>	375 mm
<b>Box Width</b>	295 mm
<b>Box Height</b>	140 mm
<b>Length</b>	235 mm
<b>Width</b>	100 mm
<b>Height</b>	75 mm
<b>Gross Weight</b>	0,261 kg
<b>Net Weight</b>	0,234 kg
<b>Cubik metre</b>	0,0018 M3
<b>Recommended sterilisation temperature (Autoclave)</b>	121 °C
<b>Max. cleaning temperature (Dishwasher)</b>	93 °C
<b>Max usage temperature (food contact)</b>	100 °C
<b>Max usage temperature (non food contact)</b>	100 °C
<b>Min. usage temperature</b>	-20 °C
<b>Min. pH-value in usage concentration</b>	2 pH
<b>Max. pH-value in Usage Concentration</b>	8 pH
<b>Gtin-13 Number</b>	5705020550072
<b>GTIN-14 Number (Box quantity)</b>	15705020550079
<b>Commodity Code</b>	39241000
<b>Country of origin</b>	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.