

R.240AT – 1/4" Universal Joint



Description:

- Universal joint
- Chrome Plated Satin Finish – improves corrosion resistance
- For Manual Use
- ISO 3316 - DIN3123 – ISO 1174-1

	Square Drive	Diameter (mm)	Length (mm)	Weight (g)
R.240AT	1/4"	14	25	22