

# Datasheet

## Stock No: 470-235

# RS Pro IDC Plug



## Product Details

### Line & Handset Plugs & Sockets

All have 'A' polarisation and are designed to accept cordage to BT specification CW 1311. Features include insulation piercing contact (IDC) termination and strain relief.

Maximum Working Voltage	200V ac
Initial Contact Resistance	0.015Ω (Plug to socket)
Insulation	10 <sup>3</sup> MΩ at 500V dc Temp. Range 0.70°C

### Connector Accessories

#### Modular sockets

Series SS 63, 64 and 65.

A series of 4, 6, 8 and 10 pin modular sockets for PCB mounting that meet the requirements for flawless communication and data transmission.

The sockets are made of black polyester (PE) with gold-plated phosphor bronze contacts; 30 µinch gold (Au) over 75 µinch nickel (Ni).

The series includes a number of variants:

Standard, series 63 (horizontal)

Low profile, series 64

Vertical, series 65

Unflanged, type NF

With panel stop, type FLS

With full flange, type F

With code (key)

With thicker gold plating on contacts.

## Specifications:

Accessory Type

IDC Plug