

Main

Range	Linergy
Product name	HK
Product or component type	Mounting plate
Poles description	3P + N
[I _{th}] conventional free air thermal current	50 A
I ² t on activation	200000 A ² .s
Number of cables	4 cable(s) 4 mm ² at 105 °C 4 cable(s) 4 mm ²
Width	106 mm
Height	190 mm
Depth	63 mm





Complementary

[Ui] rated insulation voltage	690 V conforming to IEC 60439-1
9 mm pitches	12
Net weight	0.71 kg

Environment

Standards	IEC 60439
Product certifications	UL[RETURN]CSA[RETURN]LROS (Lloyds register of shipping)[RETURN]DNV

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes