




---

 PRODUCT-DETAILS

# BEY38-4KF

## BEY38-4KF Connection Set for Star-Delta Starter




---

### General Information

Extended Product Type	BEY38-4KF
Product ID	1SBN082323R2000
EAN	3471523007710
Catalog Description	BEY38-4KF Connection Set for Star-Delta Starter

Long Description	<p>BEY38-4KF is a connection set used to connect the main poles of the Line, Delta and Star contactors of a star-delta starter for AF26..K ... AF38..K, AFC26..K ... AFC38..K contactor ranges.</p> <p>The connection sets are made up of:</p> <ul style="list-style-type: none"> <li>• Line contactor / delta contactor: upstream phase-to-phase connection</li> <li>• Delta contactor / star contactor: downstream connection in parallel             <ul style="list-style-type: none"> <li>• Star contactor: star point upstream                 <ul style="list-style-type: none"> <li>• Insulated, solid copper bar</li> </ul> </li> </ul> </li> <li>• Black fork pieces for a quick dismounting of line, delta and star contactors.</li> </ul> <p>With the Push-in Spring terminals, one push is all you need for a faster than ever installation, an easier than ever wiring and a reliable as ever connection.</p>
------------------	---

---

### Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85389099

## Popular Downloads

Data Sheet, Technical Information	1SBC100214C0202
Instructions and Manuals	1SBC101057M6801
Instructions and Manuals (Part 2)	1SAC200017M0002
CAD Dimensional Drawing	2CDC001079B0201

## Dimensions

Product Net Width	79 mm
Product Net Depth / Length	30 mm
Product Net Height	39 mm
Product Net Weight	0.09 kg

## Technical

Standards	EN 60947-1, EN 60947-4-1, UL 60947-4-1, CSA C22.2 No. 60947-4-1
Rated Operational Voltage	Main Circuit 690 V AC
Rated Frequency (f)	Main Circuit 50 / 60 Hz
Terminal Type	Push-in Spring Terminals
Suitable For	AF26 AF26Z AF30 AF30Z AF38 AF38Z
Product Name	Connection Set

## Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2021-006202
RoHS Declaration	2CMT2021-006277
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

## Certificates and Declarations

Declaration of Conformity - CE	1SBD250021U1000
Declaration of Conformity - UKCA	1SBD250043U1000
GOST Certificate	GOST_POCCFR.ME77.B07175.pdf
UL Certificate	UL-US-L312527-151-12119002-5 UL-CA-L312527-451-12119002-5

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	44 mm
Package Level 1 Depth / Length	83 mm
Package Level 1 Height	43 mm

Package Level 1 Gross Weight	0.105 kg
Package Level 1 EAN	3471523007710

---

### External Classifications and Standards

---

ETIM 7	EC002498 - Accessories for low-voltage switch technology
ETIM 8	EC002498 - Accessories/spare parts for low-voltage switch technology
ETIM 9	EC002498 - Accessories/spare parts for low-voltage switch technology
eClass	V11.0 : 27371392
UNSPSC	39121521
IDEA Granular Category Code (IGCC)	4727 >> Motor starter controls
E-Number (Finland)	3709752
E-Number (Norway)	4115835
E-Number (Sweden)	3210707

---

### Categories

---

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

