

Datasheet

Zinc Plated Toggle Latch, 250kg Op. Tension, 111 x 49 x 10.5mm

RS Stock number [186-1395](#)



Description:

Two latches with a flat profile that are especially suitable for use in areas of low clearance. The latch folds flat in the open position to minimise the risk of accidental damage. Can be used for gripping in a groove without use of the catch plate. Weld or M3 screw fixing. Latch to catch distance 52.6mm.

Features:

- Dimensions 111 x 49 x 10.5mm
- Finish Zinc Plated
- Length 111mm
- Material Steel
- Operating Tension 250kgf