

SS-3R 20X7 WH - Contactor marker



0807740

<https://www.phoenixcontact.com/gb/products/0807740>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker sheet, for Siemens SIRIUS 3R switchgear series, 40-section, 20 strips à 2 markers, labeling with M-PEN, CMS system or BMKT labels, lettering field: 20 x 7 mm

Commercial data

| | |
|--------------------------------------|--------------------|
| Item number | 0807740 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG2413 |
| Product key | BG2413 |
| Catalog page | Page 435 (CL-2005) |
| GTIN | 4017918156954 |
| Weight per piece (including packing) | 12.4 g |
| Weight per piece (excluding packing) | 9.7 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

SS-3R 20X7 WH - Contactor marker



0807740

<https://www.phoenixcontact.com/gb/products/0807740>

Technical data

Product properties

| | |
|--------------|----------------|
| Product type | Device marking |
| Pitch | 20 mm |
| Type | flat |

Marking

| | |
|-------------------------------------|----|
| Number of individual labels | 40 |
| Number of individual labels per row | 2 |
| Number of marker strips | 20 |

Mounting

| | |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

Material specifications

| | |
|--|------------------|
| Color | white (RAL 9010) |
| Material | ABS |
| Flammability rating according to UL 94 | V0 |
| Base element material | ABS |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

Dimensions

| | |
|--------|-------|
| Width | 7 mm |
| Length | 20 mm |
| Pitch | 20 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 20 mm |
| Text field height | 7 mm |

Standards and regulations

| | |
|-----------------|----------------|
| Wipe resistance | DIN 30646 |
| | DIN VDE 0611-1 |

Notes

| | |
|---------|-------------------------|
| General | Can be labeled with CMS |
|---------|-------------------------|

SS-3R 20X7 WH - Contactor marker



0807740

<https://www.phoenixcontact.com/gb/products/0807740>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
|-------------|----------|

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001288 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

SS-3R 20X7 WH - Contactor marker



0807740

<https://www.phoenixcontact.com/gb/products/0807740>

Environmental product compliance

| | |
|---|----------------------------|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk