



Multi Purpose



Oil



Light Duty

Light-duty safety gloves delivering excellent grip and abrasion and oil protection

- **Optimized protection:** Reinforced with two layers of nitrile coating and a rough palm, EDGE[®] 48-919 durable work gloves combine superior grip with abrasion and oil repellence and keep hands dry and comfortable when handling oily parts and tools
- **Enhanced defenses:** These multipurpose industrial gloves are made of a seamless liner that is fully dipped in NBR coating to protect against industrial fluid exposure, and boast EN 420 (general requirements) and EN 388 (mechanical hazards) compliance
- **Improved features:** EDGE[®] 48-919 high-quality work gloves are inexpensive and offer an elastic knitwrist and other great features, which make them ideal for workers who handle small and medium-sized components that are coated with oils and lubricants
- **Food handling compliance:** In addition, these food gloves comply with FDA food handling requirements and the Commission Regulation (EC) No. 1935/2004 as well as the Regulation (EC) No. 2023/2006 related to Good Manufacturing Practices (GMP) for materials and articles intended to come in contact with foodstuffs



Industries

- Automotive
- Construction
- Machinery and Equipment
- Metal fabrication
- Chemical
- Oil and gas
- Food Processing

Applications

- Assembly of parts
- Maintenance
- Metal Fabrication
- Quality control
- Food Processing

Key Features

- **Double layer nitrile coating:** Safer handling of oily parts and tools
- **Reduced mechanical risks:** Satisfy EN 420 and EN 388 safety standards
- **Elastic knitwrist:** For protective gloves with a snug fit

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4121A



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
EDGE [®] 48-919	Finishing: Fully Dipped Coating Material: Nitrile Liner Material: Polyester Cuff Style: Knitwrist	15	6, 7, 8, 9, 10, 11	220-280 mm, 8.66-11.02 inches	Black and Red	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306.
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699