

**IMPROVED**Vertical pocket
with zipperAdjustable waist
fastening for
improved fitSide pockets
with flaps to
prevent debris**PRODUCT INFORMATION****COLOUR:** HV Orange**FABRIC SPECIFICATION:**
ProGARM VXS+ Inherent Woven
Fabric, HV Orange - 290gms**PRODUCT CARE:****LIFETIME SEAM
GUARANTEE****VXS+
INHERENT™****4608**

JACKET

SIZES: S-4XL

- ✓ Mandarin collar for maximum neck protection
- ✓ Vertical chest pocket with zipper // Discreet design
- ✓ Gas monitor loop // Secure fixing point
- ✓ SafetyICON™ on arm // Visual EN Standard icon system
- ✓ 5cm FR AS reflective Tape // Double stitched for longer life
- ✓ Phone pocket on sleeve with flap // Safe and secure

- ✓ Velcro® secured cuff tabs // Close fit around wrist or gloves
- ✓ Side access pockets with flaps // Prevents entry of debris
- ✓ ThermSAFE™ plastic FR zipper // CE Certified
- ✓ Extended back // Protection when bending over
- ✓ Double stitched side seams // Lifetime quality assurance
- ✓ Easy-Stretch™ side panels // Maximum wear comfort

EN STANDARDS

EN ISO 11612: 2015	EN 1149-5: 2018	EN 61482-2: 2020	EN ISO 11611: 2015	EN ISO 20471: 2013 + A1:2016	Compliant
A1, B1, C1, F1	Pt. 5:2018 Pt. 3:2004 Charge Decay	APC 1 ATPV=9.3cal/cm² ELIM=8cal/cm²	Class 1, A1	Class 3	Issue 2

BOX TEST**ARC RATING****FABRIC****VXS+
INHERENT™**