

M18 FROP15-502X

M18 FUEL™ RANDOM ORBITAL POLISHER WITH 15 MM STROKE

- Delivering equal performance as corded random orbital polishers to complete polishing and heavy-correction applications
- 8 position speed dial selection for maximum control and best finishing results
- 15 mm orbital function for fast and efficient polishing with a free hologram finish
- Large ergonomic front grip area with overmold for easy and comfortable handling, especially when working with the tool vertically
- Lock-on function provides more comfortable and less strenuous use when polishing for longer periods
- 90° rotated battery slot with a clearance of more than 50 mm to prevent any touch points with the paint and allowing the tool to be stored in a horizontal or vertical position
- Line-lock-out function to prevent automatic start up
- Removable dust screen to prevent debris entrance, prolonging motor life
- The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



No load speed (rpm)	2,650 - 5,100
Backing pad diameter (mm)	125
Diameter of orbit (mm)	15
Weight with battery pack (EPTA) (kg)	3.2 (M18 B5)
Standard equipment	125 mm backing pad, dust screen
Kit included	2 x M18 B5 Battery packs, M12-18 FC Charger, HD Box
Article Number	4933478835