

Datasheet

RS Pro 2 Output Toroidal Transformer, 80VA, 2 x 25V ac

RS Stock No: **671-8984**



Product Details

RS Pro 2 output toroidal transformer is a small size and low weight with traditional stacked laminated transformers. It has both primary and secondary windings connected in series or parallel. This transformer has primary voltage rating of 115 V ac, 230 V ac, secondary voltage rating of 2 x 25 V ac and power rating of 80 VA. Toroidal transformer meets EN 61558, IEC 742, UL 506, UL 1411, UL 478 and CE certified.

Features and Benefits

- Low induced noise (hum)
- Low level of radiated magnetic field
- Flexible leadouts for ease of installation
- 100% electrical and flash testing

**Specifications:**

Diameter	93 mm
Dimensions	93 (dia.) x 38 mm
Height	38 mm
Maximum Operating Frequency	60 Hz
Minimum Operating Frequency	50 Hz
Number of Outputs	2
Power Rating	80 VA
Primary Voltage Rating	230 V ac
Secondary Current	1.6 A
Secondary Voltage Rating	2 x 25 V ac
Termination Type	Copper Conductor
Weight	1.04 kg
Construction	Open
Standards Met	UL 506, IEC 61558 Class II, EN 61558 Class II, VDE0570 Class II, RoHS Compliant

