
KEMET Part Number: SC-02-D100

(UALSC02D100000)



KEMET, SC-D, AC Line Filters, Common Mode, 100 uH



Dimensions		
D	23mm MAX	
Т	13mm MAX	
LL	15mm +/-2mm	
S	10mm NOM	

Packaging Specifications		
Packaging:	Tray	
Packaging Quantity:	360	
Weight:	7 g	

General Information		
Series:	SC-D	
Style:	Through-Hole	
RoHS:	Yes	
Notes:	Lead Spacing (S/S1) Are For Reference Only.	
Miscellaneous:	Temperature Rise Maximum: 40 K	

Specifications		
Voltage AC:	250 VAC	
Inductance:	100 uH	
Current:	2 A	
Temperature Range:	-25/+105°C	
DC Resistance:	70 mOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

