

DCD778D2T-QW

XR 18V 2Ah Li-Ion Brushless Impact Drill - Plastic Chuck



5035048690468



Product Description:

Hand/Soft Start 1760 RPM/65/20Nm/Concrete Drilling (mm): 30/13/13 Stroke Rate (cps/min): 0-8500/29750 Chuck Capacity (mm): 1.5-13 Plastic Chuck

Product features and benefits:

- 13mm keyless one-piece chuck with automatic spindle lock for quick and easy bit changes from a One-handed Two speeds, variable speed and left/right switch for
- maximum control 15-position adjustable torque mechanism for uniform results and optimum precision when screwing Hammer and hammer settings for multiple
- applications Improved ergonomic handle with rubber coating
- Multi-voltage multi-voltage charger for XR Li-ion batteries Part of the XR Li-Ion smart platform designed for even greater efficiency to get the job done more

- Compact 18V XR drill driver with XR 3Ah Li-ion batteries equipped with brushless motor

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Drill/Driver (x1)
- Batteries (x2)

Specifications techniques :

- Depth of wood: 30 mm
- Depth (Masonry): 13 mm Maximum Torque: 65 Nm
- Battery Capacity [Imperial]: 2.0 Ah
- Voltage
- Battery: 18V Weight (including battery): 1.6 Kg Power
- Output: 340 W Drilling Capacity (Metal): 13 mm

- Chuck Capacity: 1.5-13 mm