

## Features

- Conductor Material: 100% copper wires
- Jacket Material: PVC, Black
- Cable Length: 5M
- Easy to install and reliable connection
- Color: Black

## RS PRO DC Cables

RS Stock No.: 707853



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

This 90-degree right angle plug can easily go through a narrow gap, will never bend and damage the power supply cord. This cable is suitable for CCTV security cameras, DVRs, surveillance monitoring systems, LED lights or other 2.1\*5.5mm DC power equipment, etc.

Current: 3A.

Voltage: 12V.

Material: 2\*0.5mm<sup>2</sup> copper wire.

Polarity distinction: brown positive, blue negative.

Connector 1: DC 5.5mm x 2.1mm x 9.5mm male right angle 90 degree.

Connector 2: bare wire with terminal crimped

## General Specifications

Connector A	Male DC5.5*2.1*9.5mm
Connector A Gender	Male
Connector B	Open, terminal crimped
Connector Style	Plug, right angle
Outer Sheath Material	PVC
Sheath Colour	Brown, blue
Connector Plating	Nickel

## Electrical Specifications

Connection	Open end cable
Voltage Rating	12V DC
Maximum Power	3A

## Mechanical Specifications

Length	5m
Cable Specification	2*0.5mm <sup>2</sup> copper wire

## Operation Environment Specifications

Operating Temperature	0°C to 70°C
Storage Temperature	0°C to 70°C

## Approvals

Standards Met	RoHS, Reach
Declarations	RoHS, Reach

