

## M12 BI-O | M12™ sub compact inflator



- Compact lightweight design for fast inflation of car, light truck and compact equipment tires
- High efficiency motor & pump
- Anti-vibration stand with all rubber feet for no movement while inflating
- Auto shut-off technology inflates to users pre-selected pressure for highly accurate inflation
- Illuminated LCD display with a digital pressure and fuel gauge that displays remaining charge
- Nozzle & hose storage, easily stores 66 cm hose and attachments, with an all-brass schrader chuck
- REDLITHIUM™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life (Battery sold separately)

Hose length (mm)	660
Max. pressure (bar / PSI)	8.27 / 120
No load air delivery (l/min)	24.9
Duty cycle	50% at 10 min On and 10 min Off
Gauge accuracy (%)	±3
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933464124