



Einhell

PROFESSIONAL



Cordless Angle Grinder

TP-AG 18/125 CE Q Li - Solo

Item No.: 4431155

Ident No.: 21024

Bar Code: 4006825668797

The Professional cordless angle grinder TP-AG 18/125 CE Q Li-Solo is a member of the Power X-Change family. Powered by a powerful brushless motor. It delivers the same power as a corresponding wired appliance with 900 W. The speed can be adjusted from 3,000–10,500 rpm by means of speed electronics with LED display. The continuous speed electronics ensure constant power without loss of speed. The quick-release nut makes it possible to change the cutting disc without tools. The cordless angle grinder can be used with cutting discs up to Ø 125 mm. For comfortable handling, it is equipped with an additional handle, softstart and disc guard with quick adjustment. Delivery without cutting disc, without a battery or charger.

Features & Benefits

- Member of the Power X-Change family, 1x 18V battery required
- Brushless motor - more power and longer running time
- PurePOWER Brushless - 10 year motor warranty after registration
- Soft start and restart protection for safety and unit protection
- Toolless disc change due to quick-release nut
- Durability thanks to overload protection
- Disc guard with quick adjustment for more flexibility
- Constant electronics enables high load without speed loss
- Speed regulation – with LED display
- Additional handle - flexibly mountable in two positions
- Support surface for safe placement of the device
- Recommendation for optimal results: 2.5 Ah battery and larger
- Supplied without battery and charger (sold separately)
- Supplied without cutting and grinding wheels (sold separately)



Technical Data

- | | |
|-------------------------------------|-------------------------|
| - Disc size | 125 mm |
| - No-load speed (idle speed) Min. | 3000 min ⁻¹ |
| - No-load speed (idle speed) Max. | 10500 min ⁻¹ |
| - Max. cutting depth | 33 mm |



Logistic Data

- | | |
|--------------------------------------|--------------------|
| - Product weight (kg) | 1.7 |
| - Gross weight (kg) | 2.38 |
| - Dimensions single packaging | 350 x 155 x 130 mm |
| - Pieces per export carton | 4 Pieces |
| - Gross weight of export carton | 10.12 kg |
| - Dimensions Export Carton | 365 x 325 x 280 mm |
| - Container quantity (20"/40"/40"HC) | 3568 7136 8048 |



Available as special accessories

	Trennschutz TP-AG 18/125 CE Q Angle Grinder Accessory Item No.: 4450059 Bar Code: 4006825670028 No Name		5,2 Ah Power X-Change Plus Battery Item No.: 4511437 Bar Code: 4006825616606 Einhell Accessory
	PXC+ 18V 5-8Ah MULTI Battery Item No.: 4511600 Bar Code: 4006825665055 Einhell Accessory		PXC 18V 4,0Ah Battery Item No.: 4514079 Bar Code: 4006825674316 Einhell Accessory (Discounter)
	PXC+ 18V 4,0Ah SEALED Battery Item No.: 4511627 Bar Code: 4006825673227 Einhell Accessory		PXC+ 18V 4,0Ah Battery Item No.: 4511553 Bar Code: 4006825660869 Einhell Accessory
	PXC+ 18V 3,0Ah SEALED Battery Item No.: 4511618 Bar Code: 4006825672794 Einhell Accessory		PXC 18V 3,0Ah Battery Item No.: 4511341 Bar Code: 4006825590593 Einhell Accessory
	3,0 Ah Power X-Change Plus Battery Item No.: 4511501 Bar Code: 4006825644197 Einhell Accessory		2,0 Ah Power X-Change Battery Item No.: 4511395 Bar Code: 4006825610369 Einhell Accessory
	4,0 Ah Power X-Change Battery Item No.: 4511396 Bar Code: 4006825610376 Einhell Accessory		4-6 Ah Multi-Ah Power X-Change Plus Battery Item No.: 4511502 Bar Code: 4006825644210
	2x 18V 5,2Ah PXC-Twinpack Battery Item No.: 4511526 Bar Code: 4006825656695 Einhell Accessory		18V 4Ah PXC Plus Twinpack Battery Item No.: 4511629 Bar Code: 4006825673685 Einhell Accessory
	18V 3Ah PXC Plus Twinpack Battery Item No.: 4511631 Bar Code: 4006825673692 Einhell Accessory		2x18V 4,0Ah PXC-Twinpack CB B1 Battery Item No.: 4511489 Bar Code: 4006825638578
	2x2 Power X-Quattrocharger 4A Charger Item No.: 4512102 Bar Code: 4006825649536 Einhell Accessory		Power X-Fastcharger 4A Charger Item No.: 4512103 Bar Code: 4006825650228 Einhell Accessory
	Power X-Twincharger 3A Charger Item No.: 4512069 Bar Code: 4006825629729 Einhell Accessory		Power X-Car Charger 3A Charger Item No.: 4512113 Bar Code: 4006825655377 Einhell Accessory
	Power X-Boostcharger 8A Charger Item No.: 4512155 Bar Code: 4006825670554 Einhell Accessory		18V Battery Charger 3,0A - PXC Charger Item No.: 4514095 Bar Code: 4006825655292 Einhell Accessory
	18V 2,5Ah PXC Starter Kit PXC-Starter-Kit Item No.: 4512097 Bar Code: 4006825646962 Einhell Accessory		2x 4,0Ah & Twincharger Kit 1 PXC-Starter-Kit Item No.: 4512112 Bar Code: 4006825655766 Einhell Accessory
	18V 4-6Ah & 6A Boostcharger PXC-Starter-Kit Item No.: 4512143 Bar Code: 4006825667653 Einhell Accessory		18V 2,0Ah PXC Starter Kit PXC-Starter-Kit Item No.: 4512040 Bar Code: 4006825613681 Einhell Accessory
	5,2 Ah PXC Starter-Kit PXC-Starter-Kit Item No.: 4512147 Bar Code: 4006825675153 Einhell Accessory		18V 4,0Ah PXC Starter Kit B1 PXC-Starter-Kit Item No.: 4512042 Bar Code: 4006825613704 Einhell Accessory



4Ah PLUS PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512159
Bar Code: 4006825680331
Einhell Accessory



E-Case L with wheels
System Carrying Case
Item No.: 4540014
Bar Code: 4006825660562
Einhell Accessory



E-Case M
System Carrying Case
Item No.: 4540021
Bar Code: 4006825667721
Einhell Accessory

Battery-Running-Times

One Battery for All	 cutting ¹ (pieces)
1.5 Ah	29
2.0 Ah	38
2.5 Ah	48
3.0 Ah	57
4.0 Ah	76
5.2 Ah	98
6.0 Ah	113
8.0 Ah	151

For best performance select a battery with at least 2.5 Ah

Test setup:

1) metal - round steel Ø 12 mm - Max. electronic speed