

# 8910DPA63V14

## CONTACTOR 600VAC 60AMP DPA +OPTIONS



Download your 8910DPA63V14 datasheet



[Characteristics](#) | Documents & Downloads

### Main Hide

<b>Product or component type</b>	Definite Purpose Contactor
<b>[In] rated current</b>	60 A
<b>Motor power hp</b>	5 hp 115 V AC 1 phase 10 hp 230 V AC 1 phase 30 hp 460 V AC 3 phases 30 hp 575 V AC 3 phases 25 hp 230 V AC 3 phases
<b>Poles description</b>	3P
<b>Pole contact composition</b>	3 NO
<b>Control circuit voltage</b>	24 V AC 50/60 Hz

### Complementary Hide

<b>Product certifications</b>	CE CSA UL listed
<b>Locked rotor rated current</b>	360 A 277 V AC 300 A 460 V AC 240 A 575 V AC
<b>[Ue] rated operational voltage</b>	600 V AC
<b>Network number of phases</b>	3 phases
<b>Electrical connection</b>	Quick connect terminals
<b>Range of product</b>	DPA

### Offer Sustainability Hide

<b>Sustainable offer status</b>	Not Green Premium product
<b>RoHS (date code: YYWW)</b>	Will not be Compliant
<b>REACH</b>	Reference not containing SVHC above the threshold

### Contractual warranty Hide

<b>Period</b>	18 months
---------------	-----------