



Inner rings IR25X30X16-IS1-XL (Series IR..-IS1)

precision machined, with lubrication hole, to DIN 620

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	25 mm	
F	30 mm	Tolerance of raceway F in µm: 0/-12
B	16 mm	
	1	Number of lubrication holes
r _{min}	0,3 mm	
m	25,7 g	Mass

