



R-133

Tactile and secure cuff automotive glove.



Multi Purpose



Light Duty

Touchscreen-compatible synthetic leather safety gloves, combining grip and durability

- **Enhanced features:** RINGERS® R133 automotive gloves feature a hook and loop TPR pull tab closure, for a more secure fit around the wrist, while touchscreen-compatible thumb tips, index and middle fingers make for everyday practicality
- **Increased comfort and flexibility:** Soft, yet durable, mesh fabric at the top of the hand and lightweight material between the fingers ensure dexterous comfort and flexibility
- **Improved grip and durability:** RINGERS® R133 safety gloves' premium synthetic leather split-palm construction and wraparound index finger design enhance their grip performance and durability



Industries

- Automotive
- Automotive Aftermarket
- Food Processing
- Manufacturing
- Mining
- Recycling and Waste Disposal

Applications

- General Purpose Auto Aftermarket
- Handling structural and body components
- Body panel repair and replacement
- Oil, fluids and filter change
- Engine transmission and repair
- Tire rotation & changes
- Equipment maintenance and repair
- Driving fork lifts and vehicles
- Delivery of parts to production line
- Changing tools and dies



R-133

Tactile and secure cuff automotive glove.

Key Features

- Hook and loop TPR pull tab closure: Secure, form-fitting cuff
- Soft mesh fabric on top of hand: Optimal comfort and flexibility
- Premium synthetic leather split-palm: Enhanced grip and durability

Technologies



Touchscreen Compatible

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



2121X

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	PACKAGE
RINGERS® R133	Cuff Style: Adjustable		6, 7, 8, 9, 10, 11, 12, 13	5 pairs/bag, 24 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

