

Hot air tool

HM 1620 S

Folding box

EAN 4007841 089382

Article number 089382



series 1

1600 W

1600 W Output



300 °C / 500 °C



2 stage temperature adjustment



240 / 450 l/min.



2 air volume stages



Suitable for pluggable nozzles



VDE



CE

Function description

The HeatMatic 1620 S hot air blower is your reliable partner for a wide range of applications. Compact and powerful, it offers quick solutions for a wide range of tasks.

Technical specifications

Temperature	300 – 500 °C	Temperature scanner	No
Airflow rate	240 – 450 l/min	Fine dust filter	No
Temperature setting	2-stage	Thermal cut-out	Yes
Settings made via	multiple-stage switch	Thermostat	No
Airflow control	Settings	Dimensions (L x W x H)	252 x 86 x 200 mm
Programming function	No	PU1, net weight	0,717 kg
Residual heat indicator	No	Manufacturer's Warranty	3 years
Cool function	No	PU1, EAN	4007841089382
Motor, type	Brush motor	Output	1600 W
Heating element	Micanite heating element	Product category	Hot air tool
Mains power supply	220 – 230 V / 50 – 60 Hz		

Accessories

EAN 4007841 070519	Reflector nozzle
EAN 4007841 070311	Window nozzle
EAN 4007841 070410	Window nozzle
EAN 4007841 070113	Surface nozzle

<https://www.steinel.de>

Subject to technical modifications

03.2025 Page 1 from 2

Hot air tool

HM 1620 S

Folding box

EAN 4007841 089382

Article number 089382



Accessories

EAN 4007841 070212

Surface nozzle

EAN 4007841 034566

HL Tool Stand