


Features

- Manufactured with Bi-metal flexible spring steel for long life and excellent cutting performance.
- Shatterproof & flexible with hardended teeth for maximum wear resistance and are suitable for cutting a wide range of materials.

300mm Hacksaw Blades 24TPI (10pc)

RS Stock No.: 0757810



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Hacksaw Blade

Hacksaw Blades are manufactured with Bi-metal flexible spring steel for long life and excellent cutting performance. The blades are shatterproof & flexible with hardened teeth for maximum wear resistance and are suitable for cutting a wide range of materials.

- *Suitable for use with most Hacksaws*
- *Suitable for use on Metal, Stainless Steel, Plastic, Wood, Aluminium*
- *Shatterproof*

General Specifications

Material Code	D6AM2
Type	Hacksaw Blade
Blade Body Thickness	0.62mm
TPI	24
Heat Treatment (Yes/No)	Yes
Heat Treatment Technology	Vacuum Furnace Heat Treatment
Blade Finishing Technology	Black Paint
Teeth Technology	Milled Teeth
Working Length	300mm

Stock No.	Material Code	TPI	Working Length	Teeth Technology
XXX-XXXX 0757843	D6AM2	24	150mm	Milled Teeth
XXX-XXXX 0757844	D6AM2	18	300mm	Milled Teeth
XXX-XXXX 0757810	D6AM2	24	300mm	Milled Teeth

Approvals

Declarations	REACH DoC
---------------------	-----------

Similar Products

Stock No.	Brand	Product Name	Material Code	TPI	Working Length	Teeth Technology
XXX-XXXX 0757843	RS PRO	Hacksaw Blade	D6AM2	24	150mm	Milled Teeth
XXX-XXXX 0757844	RS PRO	Hacksaw Blade	D6AM2	18	300mm	Milled Teeth
XXX-XXXX 0757810	RS PRO	Hacksaw Blade	D6AM2	24	300mm	Milled Teeth

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories