

### BIZ5 - Bizweld Work FR Coverall

**Collection:** Bizweld™ Work

**Range:** Flame Resistant Multi-Norm

**Shell Fabric:** Bizweld Work: 100% Cotton, 330g

**Outer Carton:** 12

#### Product information

The Bizweld FR Coverall offers visible protection to the wearer. Clever design features include flame resistant reflective tape on the shoulders, sleeves and legs, the option to insert knee pads when needed, ample storage space and a rule pocket. A very popular style.

#### Bizweld™ Work

Bizweld™ Work protective clothing have been specially designed to guarantee comfort, performance and safety whilst providing effective function at all times. Bizweld™ Work has been rigorously tested to ensure total compliance with the latest international standards.

#### Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

#### Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 1 (A1+A2)

IEC 61482-2 IEC 61482-1-1 (ELIM 8.3 CAL/CM<sup>2</sup>, ATPV 10.9 CAL/CM<sup>2</sup>)

ASTM F1959/F1959M-12 (ATPV 11.2 CAL/CM<sup>2</sup> (HAF = 80.4%))



#### Features

- Protection against radiant, convective and contact heat
- Certified protection against molten metal splash
- Two chest pockets with stud closure
- Rule pocket
- Concealed stud front for easy access
- Stud adjustable cuffs for a secure fit
- Available in sizes up to 5XL
- Two tier knee pad pockets allowing two positioning options
- 8 pockets for ample storage
- 40+ UPF rated fabric to block 98% of UV rays
- Radio loops for easy clipping of a radio

## BIZ5 - Bizweld Work FR Coverall

**Commodity Code: 6211321000**

### Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777\_12872\_03\_E00\_00

### Wash Care



### Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m <sup>3</sup> )	EAN13	GTIN/DUN14
BIZ5ORRXS	Orange	43.0	28.0	58.0	1.2710	0.0698	5036108243631	25036108731934
BIZ5ORRS	Orange	43.0	28.0	58.0	1.3610	0.0698	5036108167890	25036108731927
BIZ5ORRM	Orange	43.0	28.0	58.0	1.4390	0.0698	5036108167883	25036108609059
BIZ5ORRL	Orange	43.0	28.0	58.0	1.4750	0.0698	5036108167876	25036108609042
BIZ5ORRXL	Orange	43.0	28.0	58.0	1.5990	0.0698	5036108167906	25036108609066
BIZ5ORRXXL	Orange	43.0	28.0	58.0	1.6410	0.0698	5036108167913	25036108609073
BIZ5ORRXXXL	Orange	43.0	28.0	58.0	1.7960	0.0698	5036108167920	25036108688962
BIZ5ORR4XL	Orange	43.0	28.0	58.0	1.8210	0.0698	5036108216918	25036108704099
BIZ5ORR5XL	Orange	43.0	28.0	58.0	1.8390	0.0698	5036108216925	25036108704105