

Pushbutton, 18.2 mm, screw terminal, momentary contact function, 2 NO, bezel white



fields of application

- Mechanical and system engineering
- Model construction
- Home technology



description

Pushbutton with mounting hole diameter 18.2 mm, non-illuminated, 250 V / 4 A

technical data

➤ general

Bezel color	white
Property of bezel / mushroom	opaque
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	85 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	90 °C
illuminated	No
Packaging	Box
Packaging unit	100 pcs.
net weight	16 g
Operating life	50,000 cycles
B10	65,000 cycles
Degree of protection, front side, according to DIN EN 60529	IP40 IP65 IP65 with sealing cap
MOQ order	100 pcs.
RoHS compliant	Yes
REACH compliant	Yes

➤ mounting diameters

Outside dimension, length	22 mm
Outside dimension, width	22 mm
Outside dimension, height	44.5 mm
Mounting hole	18.2 mm
Mounting depth	34 mm
Installation height	10.5 mm

➤ mechanical data

Actuation function	momentary contact function
--------------------	----------------------------

direct links

- [RAFI eCatalog](#)

Operating force, min.	9.5 N
Operating travel, max.	5 mm
Contact function	2 NO
Contact system	Bridge-sliding contact
Contact material	Silver
Fixing	Threaded ring
Terminal on the rear	Screw terminal

> electrical data

Rated voltage, max.	250 V
Rated current, max.	2 A