

Eaton 267976

Catalog Number: 267976

Eaton Distribution parts. Pre-selection relay, 24VAC/50Hz, 2N/O, 20A, 1HP

General specifications



Product Name
Eaton Distribution parts

Catalog Number
267976

EAN
4015082679767

Product Length/Depth
80 mm

Product Height
70 mm

Product Width
17.5 mm

Product Weight
0.136 kg

Compliances
RoHS conform

Product specifications

Amperage Rating

20 A

Mounting method

DIN rail

Equipment heat dissipation, current-dependent

6.4 W

Control voltage 1 type

AC

Ambient operating temperature - max

45 °C

Ambient operating temperature - min

-20 °C

Control voltage 1 - max

24 V

Control voltage 1 - min

24 V

Control voltage 2 - max

0 V

Control voltage 2 - min

0 V

Frequency control voltage 1 - max

50 Hz

Frequency control voltage 1 - min

50 Hz

Frequency control voltage 2 - max

0 Hz

Frequency control voltage 2 - min

0 Hz

Heat dissipation per pole, current-dependent

2 W

Incandescent lamp load - max

0 W

Load fluorescent lamp - max

0 VA

Load fluorescent lamp (duo circuit) - max

Resources

Declarations of conformity

[DA-DC-03_Z-TN](#)

[DA-DC-03_N2](#)

Drawings

[eaton-3d-drawing-r-pack.jpg](#)

[eaton-3d-drawing-z-r-sch-einbau.jpg](#)

[eaton-dimensions-mas-z-tn.jpg](#)

Wiring diagrams

[Z_TN_1MU_SS](#)

0 VA

Load fluorescent lamp (parallel compensated) - max

0 VA

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

0

Number of contacts (normally open contacts)

2

Control voltage 2 type

AC/DC

Rated operational current for specified heat dissipation (In)

20 A

Supply voltage - max

250 V

Supply voltage - min

250 V

Switching current (cos phi = 0.6) - max

0 A

Width in number of modular spacings

1

Built-in depth

60 mm

Voltage type

AC

Functions

Mechanical

Reserved.

owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)