



PRODUCT-DETAILS

SPLHCB25/25M**25MM GS-TPR COND SS BRD 25M-BL****General Information**

Extended Product Type:	SPLHCB25/25M
Product ID:	7TCA296100R0171
EAN:	5020963011023
Catalog Description:	25MM GS-TPR COND SS BRD 25M-BL
Long Description:	Liquid Tight, Extreme Temperature Covered Steel Flexible Conduit with Stainless Steel Overbraid, Medium Flexibility, Nominal Conduit Size 25mm, Outside Diameter 26.4mm, Inside Diameter 21.0mm, Static Bend Radius 110mm, Reel Length 25 Meters, Thermoplastic Rubber Cover with Galvanised Steel Core, Black
Display Name:	SPLHCB25/25M

Additional Information

Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Liquid Tight - Extreme Temperature Environments

Ordering

EAN: 5020963011023

UPC: 786210245515

Dimensions

Outside Diameter: 26.4 mm

Technical

Number of Batteries: 0

Color: Black

Material: Galvanized Steel Core with Thermoplastic Rubber Cover

Environmental

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963011023

Package Level 1 Height: 10 in
254 mm

Package Level 1 Depth / Length: 16 in
406 mm

Package Level 1 Width: 16 in
406 mm

Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

External Classifications and Standards

ETIM 8: EC001179 - Protective metallic hose

ETIM 9: EC001179 - Protective metallic hose

UNSPSC: 39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

