



ENGLISH

Datasheet Impact Wrenches

1/2 inch Compact Air Impact Wrench

[RS Stock No. 739-8379](#)



Specifications:

Power source	: Compressed air
Maximum permissible operating pressure	: 90 psi (6.2 bar)
Recommended operating pressure	: 90 psi (6.2 bar)
Material	: Aluminium
Size	: 1/2"
Max Torque	: 540Nm / 400 ft-lb
Vibration	: 1.39m/s ²
Sound	: 96.6dBA
Mechanism	: Pin Clutch Hammer
Free Speed	: 7,500RPM
Length	: 7.5" / 190mm
Weight	: 2.4kgs / 5.3lbs Min
Hose Size	: 3/8" / 10mm
Air Inlet thread	: 1/4"
Ave Air Consumption	: 3.6cfm / 101.7 l/min
Recommended lubrications	: 10 Weight SAE Oil

Features:

- High power output
- Pin clutch hammer mechanism
- Forward and reverse mode
- Rear exhaust through handle
- 3 forward & 3 reverse operating impact settings
- Non slip comfortable grip
- Ideal for truck, bus and farm machinery work
- Rugged design
- Single handed direction change

Declaration of Conformity

We RS Components Ltd declare under our sole 739-8379 – 3/4" Impact Wrench responsibility that the conforms with the directive 2006/42/EEC and the standards EN 792-6 ISO 28927