

Eaton 24TDMEJ16

Catalog Number: 24TDMEJ16

Fuse-link, medium voltage, 16 A, AC 24 kV, 2", 51 x 442 mm, back-up, DIN, with striker

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage DIN fuse	24TDMEJ16
	EAN
	5027590245821

UPC	Product Length/Depth
051712186308	442 mm

Product Height	Product Width
54 mm	51 mm

Product Weight	Compliances
2221 g	DIN 43625
	VDE 0670-4
	IEC 60282-1

Certifications
IEC Rated

Product specifications

Used with

270303 Fuse clip

A3354710 Fuse clip

Type

Fuse

Special features

Back-up, Transformer protection, Indoor or outdoor use

Application

transformer protection

indoor or outdoor use

Amperage Rating

16 A

Fuse indicator

With Striker

Fuse size

51 x 442 mm

Breaking capacity

50 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

DIN

Utilization category

Other

Voltage type

Resources

Technical data sheets

[720104 12kV DIN medium voltage fuses](#)

[720106 24kV DIN medium voltage fuses](#)

[720105 17.5kV DIN medium voltage fuses](#)

AC

With striker

Yes

Class

Class back-up

Barrels

1

Construction type

Bolt-on

Pre arc (I²T)

2.6 x 100

Resistance

109 Ohms

Watt losses

34 W

Fuse diameter

51 mm

Color

Brown

Interrupt rating

50 kAIC

Construction size

51 x 442 mm

Mounting method

Clip-in

Packaging type

Standard

Quantity

1

Voltage rating

24 kV

Fuse type

TDMEJ



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia