2209 : Individual Hole Saws





The + product :

Virax bi-metal hole saws, with their varying tooth height and gullet size guarantee:
A fast, regular cut.
Low vibration during cutting.
Easy removal of the blank.
Increased durability.
Low pressing force.

Description

For accurate drilling of various materials and in particular gas pipes to form welded connections. - HSS bi-metal saw. - HSS teeth of varying height and gullet size.

References

Sku	Ø "	Ø mm	H mm	kg
220910	5/8	14	38	0,023
220911	11/16	17	38	0,025
220912	3/4	19	38	0,030
220914	7/8	22	38	0,040
220916	1	25	38	0,050
220917	1.1/16	27	38	0,060
220918	1.1/8	29	38	0,070
220920	1.1/4	32	38	0,075

Sku	Ø "	Ø mm	H mm	kg
220921	1.5/16	33	38	0,080
220922	1.3/8	35	38	0,090
220924	1.1/2	38	38	0,065
220926	1.5/8	41	38	0,075
220928	1.3/4	44	38	0,085
220930	1.7/8	48	38	0,100
220932	2	51	38	0,110
220934	2.1/8	54	38	0,125
220936	2.1/4	57	38	0,140
220938	2.3/8	60	38	0,155
220940	2.1/2	64	38	0,170
220942	2.5/8	67	38	0,190
220948	3	76	38	0,230
220952	3.1/4	83	38	0,280
220956	3.1/2	89	38	0,31
220964	4	102	38	0,41
220966	4.1/8	105	38	0,410
220972	4.1/2	114	38	0,480
220980	5	127	38	0,610

