



CCG 18-125-7 AS

Cordless angle grinder, 125 mm in diameter

Compact and easy-to-use cordless angle grinder for light-duty grinding and cutting work.

Product number: 7 122 13 61 00 0

Details

- + High power, mobile use: The brushless high-power motor delivers the same power as a comparable corded 700 W tool for light-duty grinding and cutting work.
- + Optimum user protection features include restart protection, soft start and electronic overload protection.
- + Slimline handle and balanced design for perfect ergonomics.
- + Secure hold for all applications thanks to non-slip handle.
- + Safety hood, which can be adjusted without the use of tools, and quick-clamping nuts make for short setup times.
- + Compatible with all 18 V AMPShare ProCORE batteries and chargers for even more power and flexibility. Also suitable for 18 V Bosch Professional cordless devices.
- + COOLPACK 2.0 technology delivers a 135% longer battery life and therefore makes longer operating times possible.
- + State-of-the-art cell technology and intelligent battery management deliver 87% more power than with conventional batteries.
- + ProCORE Li-Ion battery with high-power cells, charge status indicator and "Electronic Cell Protection" (ECP). ECP protects against overload, overheating and total discharge.
- + Ideally equipped for every form of use. Mobile working with the L-BOXX system.

Price includes

- + 1 Tool-free quick-clamping nut
- + 1 wheel guard
- + 1 safety hood for cutter
- + 1 Inner flange
- + 1 anti-vibration handle
- + 1 tool case (L-BOXX 136)

Product feature

- + POWERtronic tacho electronics
- + Restart protection
- + Soft start
- + Electronic overload protection

Application



Deburring

++

Dividing

++

Brushing

+

+ suitable

++ well suitable

Technical data

TECHNICAL DATA

Speed, no load

11,000 rpm

Grinding disc Ø

125 mm

Elast. Backing pad Ø

125 mm

Flange

M 14

VIBRATION AND SOUND EMISSION VALUES

Sound pressure level LpA
Uncertainty of measured value
KpA

79 dB
3 dB

Sound power level LWA
Uncertainty of measured value
KWA

90 dB
3 dB

Vibration value 1 α_{hv} 3-
way
Uncertainty of measured value
K α

7,0 m/s²
1,5 m/s²

Vibration value 2 α_{hv} 3-
way
Uncertainty of measured value
K α

3,5 m/s²
1,5 m/s²

Application examples



FEIN



Powered by



BOSCH

**Kompatibel mit
AMPShare-/ Bosch
Professional 18 V
Akkus.** | Compatible
with AMPShare/Bosch

Professional 18 V batteries. | Compatible avec
les batteries 18 V AMPShare/Bosch Professional. |
Compatible con baterías AMPShare/Bosch
Professional de 18 V. | Compatibile con le batterie
AMPShare / Bosch Professional da 18 V.

