



## J.S.T. (U.K.) LTD. CRIMP SPECIFICATIONS

<b>TERMINAL PART NUMBER</b>	SSHL-002T-P0.2
<b>STRIP LENGTH (MM)</b>	1.5

APPLICABLE WIRE SIZE	CONDUCTOR BARREL		INSULATION BARREL		TENSILE (NEWTONS)
	HEIGHT	WIDTH	HEIGHT	WIDTH	
30 AWG	0.44~0.48	0.7	*	0.85	5N
28 AWG	0.48~0.52	0.7	*	0.85	10N
26 AWG	0.52~0.56	0.7	*	0.85	20N

### COMMENTS:

\* INSULATION CRIMP HEIGHT IS DEPENDANT ON THE SPECIFICATION OF THE WIRE USED.

CRIMP HEIGHTS SPECIFIED ARE FOR GUIDANCE ONLY AND MAY VARY DEPENDING ON THE WIRE CONSTRUCTION AND TOLERANCE.

### GENERAL TOLERANCE:

CONDUCTOR HEIGHT	See above
CONDUCTOR WIDTH	- +/- 0.05
INSULATION HEIGHT	- N/A
INSULATION WIDTH	- +/- 0.05

FOR SPECIFIC WIRES PLEASE CONTACT J.S.T. (U.K.) LTD.

Prepared by:	Approved by:
PDS 10-11-06	PDS 10-11-06