

Snap frame aluminium OUTDOOR A2

Article number	504623	Sales unit quantity	1 Piece
Colour	Silver	Sales unit EAN	4005546745473
Packaging unit	piece	Packing weight (gross)	1210.6 G
Base EAN	4005546745473	Country of origin	CN



Product description

- Durable aluminium frame for long-term indoor and outdoor use. Perfect for professionally displaying information
- Quick and easy to change the insert thanks to the easy frame opening
- Internal rubber seal provides effective protection against water ingress (Protection rating IPX4 according to DIN EN 60529)
- Clear readability in all lighting conditions thanks to UV-resistant anti-glare cover
- Clean, seamless appearance without visible joints, achieved through precisely mitred frame corners
- Flexible and safe mounting on various surfaces is enabled by screw or adhesive installation, which is included
- The frames can be easily installed and used in either portrait or landscape formats
- Snap frame metal width: 25mm

Product features

Outer width (mm)	470
Outer height (mm)	645
Outer depth / length	12 mm
Filling quantity / Filling quantity for	1 Sheet
Format / Format for	A2
Orientation Format	Portrait / landscape
Brand	DURABLE

Snap frame aluminium OUTDOOR A2

Width of Visible Area (mm)	420
Height of Visible Area (mm)	592
Frame width (mm)	12
Attachment type	Self-adhesive + Screw set
Surface product can be used on	Diverse surfaces
Frame can be opened	Yes
Read from both front and back	No
Frame looks identical on both sides	Yes
UV Resistance	Up to 2 years
Heat Stability	Up to approx. 50°
Cold Stability	Up to approx. - 20°
Anti-glare / minimises reflections	Yes
Application area	Outdoor