



HelaTape Wrap - Vinyl Tapes

HelaTape Wrap 25 - Vinyl Tape for Corrosion Protection

Features and Benefits

- Special adhesive
- Excellent protection against corrosion
- Complete environmental, mechanical and electrical protection
- Highly resistant to UV, water, oil, most chemicals, bacteria and fungus
- Used for pipes, tubes, and conduits in outside and underground applications



HelaTape Wrap 25 can be used for both overhead and direct burial applications.

MATERIAL	Polyvinylchloride (PVC)
Dielectric Strength	40 kV/mm
Adhesion to Steel	2.4 N/10 mm
Adhesion to Backing	2.0 N/10 mm
Elongation at break	250 %
Breaking Strength	48 N/10 mm
Operating Temperature	+105 °C

RoHS ✓

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-WRAP25-25x30	0.25	25.0	30.0 m	Black (BK)	710-00800
HTAPE-WRAP25-38x30	0.25	38.0	30.0 m	Black (BK)	710-00801
HTAPE-WRAP25-50x30	0.25	50.0	30.0 m	Black (BK)	710-00802
HTAPE-WRAP25-100x30	0.25	100.0	30.0 m	Black (BK)	710-00803

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content.