

# SHOWA

## CS710

CHEMICAL PROTECTION

### Oil grip nitrile coated glove with 30cm cuff

Offering high resistance to chemicals & excellent oil grip properties. For demanding tasks that require manual exertion & complete control over work materials in oily handling conditions.

#### Features

- ▲ A fine, durable glove (1.47mm thick)
- ▲ Nitrile protects the hand from oils, hydrocarbons, & grease penetration
- ▲ Foam finish provides a tactile feel, long-lasting grip, & control in oily conditions
- ▲ Impermeable for working in oily environments
- ▲ Designed for easy movement & continuous wear
- ▲ Excellent abrasion resistance
- ▲ Seamless knit designed to prevent irritation
- ▲ Anatomically formed

#### Certifications



#### Suitable industries & applications

##### Industries

- ▲ Food Production
- ▲ Healthcare
- ▲ Construction
- ▲ Manufacturing
- ▲ Chemicals
- ▲ Oil and Gas
- ▲ Home and Garden

##### Applications

- ▲ Component and Product Assembly
- ▲ Chemical Handling and Containment
- ▲ Commercial Cleaning
- ▲ Fossil Fuel Extraction and Refining
- ▲ General Maintenance
- ▲ Metal Forging and Processing

##### Europe

sales@globus.com  
+44 (0)161 877 4747  
+44 (0)161 877 4746

##### Middle East & Africa

sales.gcc@globusgroup.com  
+971 4 882 9962  
+971 4 882 9963

##### Americas

salesusa@globusgroup.com  
+1 83 337 54747

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

**GLOBUS**

# SHOWA

## CS710

CHEMICAL PROTECTION

Oil grip nitrile coated glove with 30cm cuff

### Product information

<b>Materials</b>	Liner:	Polyester
	Coating:	Nitrile
<b>Colour</b>	Blue / Black	
<b>Length</b>	450mm	
<b>Cuff Style</b>	Gauntlet	

### Ordering information

<b>S</b>	SHOCS7101	Items per Pack 10 x Pairs
<b>M</b>	SHOCS7102	
<b>L</b>	SHOCS7103	Items per Case 60 x Pairs
<b>XL</b>	SHOCS7104	
<b>XXL</b>	SHOCS7105	

### Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

#### Europe

sales@globus.com  
+44 (0)161 877 4747  
+44 (0)161 877 4746

#### Middle East & Africa

sales.gcc@globusgroup.com  
+971 4 882 9962  
+971 4 882 9963

#### Americas

salesusa@globusgroup.com  
+1 83 337 54747

**Globus Group**, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM  
**Globus EMEA FZE**, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES  
**Globus Americas LLC**, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.  
The manufacturer reserves the right to make any modifications it deems necessary.

 **GLOBUS**