



## 20683-787 Polo shirt

Premium - Modern fit

MASCOT® CROSSOVER



60% organic cotton/40% recycled polyester  
180 g/m<sup>2</sup>



Pique fabric. Shrinkage max. 5%. Colour 08: 90% organic cotton/10% viscose.

### Industrial care category C2

### Certifications



### Logo

#### Logo placement:

- Workwear logo. Left breast. Max 10x10 cm/3.9x3.9 inches
- Workwear logo. Right breast. Max 10x10 cm/3.9x3.9 inches
- Workwear logo. Mid-back. Max 28x28 cm/11x11 inches
- Workwear logo. On the nape. Max 12x5 cm/4.7x1.9 inches
- Workwear logo. Horizontal on right sleeve. Max 10x5 cm/3.9x1.9 inches
- Workwear logo. Horizontal on left sleeve. Max 10x5 cm/3.9x1.9 inches
- Workwear logo. Left flip. Max 8x2 cm/3.1x0.7 inches
- Workwear logo. Right flip. Max 8x2 cm/3.1x0.7 inches
- Workwear logo. Special placement. Contact to discuss further



- The organic cotton is grown without the use of pesticides or chemicals.
- Recycled polyester is made from collected and recycled plastic.
- The fabric dries quickly and retains its colour and shape after every wash.
- The fabric has a high wear resistance and therefore lasts longer overall.

### Technical info

Premium. Modern fit. Buttoned placket. Ribbed collar and cuffs. Neckband.

### User

