



ENGLISH

Datasheet

RS PRO enclosure, PC, 289x239x107mm

Stock No: 197-2017



Technical Specifications:

Material	Polycarbonate
Dimensions (LxWxH)	289x239x107 mm
Colour	Base: RAL 7035 – light grey Cover: RAL 7035 – light grey
IP Rating	IP 65
IK Rating	IK 07/IK08
Electrical insulation	Totally insulated
Flammability Rating	UL 746C 5"
renro com	

rspro.com

Features & Benefits:

- Ouickly assembled with rapid hinge
- Compatible with all standard PVC enclosures
- Halogen free
- Good chemical resistance
- Temperature Range from -40° to +120°, short term
- Temperature Range from -40° to +80°, continuous
- Including:

Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensional line drawings





