



Part Number : [1301120156](#)
Product Description : Construction Guard 1-1/2"
Neck Zinc Plated
Series Number : 130112
Status : Active
Product Category : Portable Lighting Accessories
Engineering Number : 367



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Portable Lighting Accessories
Series	130112
Description	Construction Guard 1-1/2" Neck Zinc Plated
NEMA Configuration	N/A
Product Name	Safety Yellow
Type	Accessory
UPC	78678861167

Electrical

Lamp Wattage - Maximum	N/A
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	N/A

Physical

Bulb Type	N/A
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	120.65mm (4.750")
Duty	Commercial
Guard Included	Yes
Guard Type	Steel
Height	149.35mm (5.880")
Lamp Type	A21
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Net Weight	149.685/g
Outlet	None
Packaging Type	Carton