



regulator plate

VABF-S3-1-R5C2-C-6

Part number: 543541

FESTO

For valve terminal VDMA-01/02, standard port pattern to 15407-1, up to 6 bar.



Data sheet

Feature	Value
Width	26 mm
Based on the standard	ISO 15407-1
Assembly position	Any
Pneumatic vertical stacking	Pressure regulator for 2 and 4 reversible
Controller function	Output pressure constant with secondary exhaust
Pressure gauge selection	possible
Pressure regulation range	0.5 ... 6 bar
Inlet pressure 1	0.5 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
Protection class	IP65 NEMA 4
Ambient temperature	-5 ... 50 °C
Product weight	430 g
Vertical stacking type of mounting	on manifold block on individual sub-base
Pressure gauge connection	with retaining clamp
Materials note	Conforms to RoHS
Material control panel	PA
Material regulator housing	Aluminium die cast