

# 1" TORQUE WRENCH PLUS 400 - 2000 NM

- 1" torque wrench
- $\pm 4\%$  accuracy
- 72-teeth ratchet mechanism compliant with DIN 3122
- Twist reverse and quick-release button for socket changes
- 5-degree swing arc for precise adjustments in confined spaces
- Locking device to prevent accidental torque setting changes
- Clear Nm scale for quick and reliable settings
- Ergonomic bi-material handle with hand placement markings
- Delivered in a durable storage case
- Individually tested to ISO 6789 standards with unique serial number and Declaration of Conformance



TengTools 1192P2000 1" torque wrench Plus is intended for professional users performing precision tasks within a torque range of 400–2000 Nm, such as maintaining large mining machinery, assembling industrial equipment, or applications in the shipbuilding industry. The torque wrench is designed for torques between 400–2000 Nm, with an accuracy of  $\pm 4\%$ . It features a DIN 3122-compatible 72-teeth ratchet mechanism with twist reverse and quick-release button for easy socket or accessory changes. The ratchet mechanism has a 5° swing arc and is built for clockwise fastening of right-hand threads. A clear Nm scale with a resolution of 10 Nm makes it easy to achieve precise settings. The click-type mechanism provides an audible and tactile signal when the required torque is reached, preventing over-torquing. The locking function ensures that the setting is maintained and does not change accidentally during use. The handle is designed for comfort and ergonomics with a non-slip bi-material grip, marked to show where to place the hand for proper force application. The tool weighs 13.35 kg, is 2216 mm long, and 84 mm wide. For easy transport and protection in demanding environments, the torque wrench comes with a durable storage case. Each torque wrench is assigned a unique number and individually tested to comply with ISO 6789 standards and comes with a 'Declaration of Conformance' for guaranteed accuracy.

## General information

**Country of origin:** Taiwan  
**Barcode:** 5020385034051  
**Tariff code Europe:** 8204120000  
**ECCN US:** EAR99  
**ETIM:** EC002132  
**UNSPSC:** 27111715

## Features

1"

## Attributes

**Product type:** Torque Wrenches  
**Drive:** 1"  
**Number of teeth:** 72  
**Range:** 400-2000 Nm  
**Scale resolution:** 10  
**Accuracy:**  $\pm 4\%$   
**Calibration certificate:** Factory  
**Reverse direction:** Twist  
**Preset:** No  
**Angular gauge:** No  
**Digital:** No  
**Bi-directional:** No  
**Mechanism:** Click  
**Tethering facility:** No

## Dimensions

**Net weight (g):** 13350  
**Width (mm):** 84  
**Length:** 2216 mm



## DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.

Technical changes and errors may occur. 04-02-2025 09:18



Sandbergsvägen 3  
 441 39 Alingsås,  
 Sweden