

Angle Grinder XGT®

GA049G

40Vmax, 115 mm, 11 000 min⁻¹

Model GA049G is a 115 mm (4-1/2") angle grinder powered by 40Vmax XGT® Li-Ion battery

The new housing structure provides high rotation speed similar to that of corded models. Other features and benefits are: Slide lever style wheel cover, Paddle switch.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	11000 min ⁻¹
Spindle Thread	M14
Bore Size (Arbor Diameter)	22,23 mm
Disc Diameter	115 mm
Anti-Restart Function (NVR Switch)	✓
Electronic brake	✓
Sound Power Level (L _{WA})	93 dB(A)
Sound Pressure Level (L _{pA})	85 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Tool weight with battery	3,0 - 5,4 kg
Product Dimensions (L x W x H):	410 x 130 x 169

User benefits

- Brushless maintenance-free and long-life motor

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing