



MINI IMPACT WRENCH 1/2", S1 SERIES

RC2751

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:34





DESCRIPTION

MINI IMPACT WRENCH 1/2", S1 SERIES

PRACTICAL: Tightening / loosening reversal with one pushbutton, 3 tightening speeds and 1 loosening speed.
COMFORT: Two-material handle for greater comfort.

Lightweight 1/2" wrench with high power-to-consumption yield. Ideal for use in confined spaces.

Lightweight 1/2" impact wrench with high power/consumption ratio

- Max. loosening torque : 620 Nm
- Working consumption : 120 l/min
- Rotation speed : 9 000 rpm

Ideal with a 200l/min hose

3 possible speeds of rotation:

- Speed 1 : 270 to 340 Nm

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:34



- Speed 2 : 475 to 540 Nm
- Speed 3 : 540 to 620 Nm

SPECIFIC DATA

Designation	MINI IMPACT WRENCH 1/2"
Sales reference	RC2751
L (mm)	122
Weight (g)	1550
Rotation speed (rpm)	9000
Vibration (m/s²)	9,7
Noise level (dBa)	89
C mm	6,5
C min mm	
C mm	1/4
Maximum input torque Nm	620
Hammer type	
Guarantee	M2 SAM Equipment and Machine Guarantee

Guarantee applied

M2 | SAM Equipment and Machine Guarantee

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

