# GRM21BC8YA106KE11# "#" indicates a package specification code.
















< List of part numbers with package codes > GRM21BC8YA106KE11L

### **Shape**



2.0 ±0.2mm
1.25 ±0.2mm
1.25 ±0.2mm
0.2 to 0.7mm
0.7mm min.
0805 (2012M)

#### **Notes**





Packaging	Specifications	Minimum quantity
L	ф180mm Embossed taping	3000

Mass (typ.)		
1 piece	23mg	
φ180mm Reel	118g	

## **Specifications**

Capacitance	10μF ±10%
Rated voltage	35Vdc
Temperature characteristics (complied standard)	X6S(EIA)
Capacitance change rate	±22.0%
Temperature range of temperature characteristics	-55 to 105°C
Operating temperature range	-55 to 105°C

1 of 2




<sup>1.</sup> This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





<sup>2.</sup> This datasheet has only typical specifications because there is no space for detailed specifications.


#### Chart of characteristic data (The charts below may show another part number which shares its characteristics.)














2 of 2



<sup>1.</sup>This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

<sup>2.</sup> This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.