

1594

lever bar clamps

	art.	A ~	A max mm	L1 mm
015940020	1594 200	200	240	145
015940025	1594 250	250	290	145
015940030	1594 300	300	340	145
015940040	1594 400	400	430	150
015940050	1594 500	500	530	150
015940060	1594 600	600	630	150

